Teflon[®] PTFE 7A

Granular Compression Molding Resin

Brand

Teflon[®] is a registered trademark of DuPont for its brand of fluoropolymer resins, which can only be licensed by DuPont for use in approved applications. Customers who wish to use the *Teflon*[®] trademark in connection with DuPont PTFE products under license from DuPont should contact (800) 262-2745. Without a license, customers may not identify their product as containing *Teflon*[®], but may refer to the resin as PTFE 7A.

Description

Teflon[®] PTFE 7A is a white powder with very small particle size. Its most unique feature is high bulk density.

The small particle size of *Teflon*[®] PTFE 7A helps to minimize voids even at relatively low molding pressure. High bulk density increases the size of moldings possible from a given mold or press opening.

Teflon[®] PTFE 7A is preferred for large moldings, such as billets, requiring optimum mechanical and electrical properties. It is also used in a mixture with fillers when they are added to modify the mechanical properties of moldings.

Properly processed products made from neat *Teflon*[®] PTFE 7A provide the superior properties typical of the fluoropolymer resins: retention of properties after service at 260°C (500°F), useful properties at -240°C (-400°F), chemical inertness to nearly all industrial chemicals and solvents, and

low friction and antistick surfaces. Dielectric properties are outstanding and stable with frequency and temperature. Molded products have moderate stiffness and high ultimate elongation.

In a flame situation, products of *Teflon®* PTFE 7A resist ignition and do not themselves promote flame spread. When ignited by flame from other sources, their contribution of heat is small and with very little smoke.

Statements, or data, regarding behavior in a flame situation are not intended to reflect hazards presented by this or any other material when under actual fire conditions.

Typical End Products

Many end products are fabricated from moldings of *Teflon*[®] PTFE 7A, including skived film and sheet, gaskets, packings, mechanical seals, bridge or pipeline bearing pads, shaft bearings, electrical insulators, piston rings, expansion bellows, diaphragms, and chemical linings. The use of fillers provides a wide choice of modified mechanical properties.

FDA Compliance

Properly processed products (sintered at high temperatures common to the industry) made from *Teflon®* PTFE 7A resin can qualify for use in contact with food in compliance with FDA Regulation 21 CFR 177.1550.

Teflon® is a registered trademark of DuPont.

Processing

Teflon® PTFE 7A usually is processed in two steps: preforming and sintering. The powder is first compacted into a preformed shape approximating that of the desired molding. A precise heating (sintering) and cooling cycle is then used to consolidate the molding at temperatures above the crystalline melting point of the neat powder. The properties of a finished molding are dependent on preform pressure, sintering time and temperature, and cooling rate.

Teflon® PTFE 7A is used to make relatively large objects in molds that can be filled manually. Small-particle resins do not flow properly in automatic feeding systems. Refer to the typical property data in **Table 1**.

Safety Precautions

WARNING!

VAPORS CAN BE LIBERATED THAT MAY BE HAZARDOUS IF INHALED.

Before using *Teflon®* PTFE 7A, read the Material Safety Data Sheet and the detailed information in the "Guide to the Safe Handling of Fluoropolymer Resins," latest edition, published by the Fluoropolymers Division of The Society of the Plastics Industry—available from DuPont. Open and use containers only in well-ventilated areas using local exhaust ventilation (LEV). Vapors and fumes liberated during hot processing, or from smoking tobacco or cigarettes contaminated with *Teflon®* PTFE 7A, may cause flu-like symptoms (chills, fever, sore throat) that may not occur until several hours after exposure and that typically pass within about 24 hours. Vapors and fumes liberated during hot processing should be exhausted completely from the work area; contamination of tobacco with polymers should be avoided.

Mixtures with some finely divided metals, such as magnesium or aluminum, can be flammable or explosive under some conditions.

Storage and Handling

Preforming is easiest when the resin is uniformly between 21–27°C (70–80°F). As temperature declines below this range, the resin will be increasingly difficult to mold without cracks and problems with condensed moisture. Higher temperatures inhibit flow and promote lumping. Storage conditions should be set accordingly.

Cleanliness is a critical requirement for successful use of *Teflon®* PTFE 7A. The white resin and high sintering temperatures cause even very small foreign particles to become visible in finished moldings. Keep resin drums closed and clean. Good housekeeping and careful handling are essential.

Property	ASTM Test Method	Unit	Nominal Value
General			
Average Bulk Density	D4894	g/L	460
Average Mold Shrinkage (at preform pressure of 35 MPa [5,000 psi])	D4894	%	3.4
Average Particle Size	D4894	μm	34
Standard Specific Gravity	D4894		2.16
Melting, Peak Temperature Initial Second	D4894	°C (°F) °C (°F)	342 ±10 (648 ±18) 327 ±10 (621 ±18)
Mechanical			
Tensile Strength	D4894	MPa (psi)	34.5 (5,000)
Elongation at Break	D4894	%	375

 Table 1

 Typical Property Data for Teflon[®] PTFE Fluoropolymer Resin Grade 7A*

* Teflon[®] PTFE 7A is ASTM D4894, Type II.

Note: Typical properties are not suitable for specification purposes.

Freight Classification

Teflon® PTFE 7A, when shipped by rail or express, is classified "Plastics, Synthetic, O.T.L., NOIBN." Resin shipped by truck is classified "Plastics, Materials Granules."

Packaging

Teflon[®] PTFE 7A is packaged in 100-lb (45-kg) drums. Each drum has a bag liner made of polyethylene resin.

For more information on Fluoroproducts:

(302) 479-7731

DuPont Fluoroproducts P.O. Box 80713 Wilmington, DE 19880-0713

Europe

DuPont de Nemours Int'l SA **DuPont Fluoroproducts** 2, chemin du Pavillon P.O. Box 50 CH-1218 Le Grand-Saconnex Geneva, Switzerland (022) 7175111

Latin America

Du Pont Fluoroproducts Latin America Regional Office P.O. Box 80702 Wilmington, DE 19880-0702 (302) 999-3582

Japan and Asia Pacific

DuPont Mitsui Fluorochemicals Co., Ltd. Chiyoda Honsha Building 5–18, Sarugaku-cho 1-chome Chiyoda-ku, Tokyo 101 Japan 81-3-5281-5872

Canada

DuPont Canada, Inc. **DuPont Fluoroproducts** P.O. Box 2200, Streetsville 7070 Mississauga Road Mississauga, Ontario, Canada L5M 2H3 (905) 821-5925

The information set forth herein is furnished free of charge and is based on technical data that DuPont believes to be reliable. It is intended for use by persons having technical skill, at their own discretion and risk. The handling precaution information contained herein is given with the understanding that those using it will satisfy themselves that their particular conditions of use present no health or safety hazards. Because conditions of product use are outside our control, we make no warranties, express or implied, and assume no liability in connection with any use of this information. As with any material, evaluation of any compound under end-use conditions prior to specification is essential. Nothing herein is to be taken as a license to operate under or a recommendation to infringe any patents.

CAUTION: Do not use in medical applications involving permanent implantation in the human body. For other medical applications, see "DuPont Medical Caution Statement," H-50102.

